

JW606HPL Cut Sheet



Stahlin JW series enclosure, NEMA 1/3R/4X/6P/12, 6 x 6 x 4in (HxWxD), wall mount, fiberglass reinforced polyester, gray, single-door, (1) quick-release latch, padlock hasp and staple, SAR acrylic window.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/JW606HPL>

Technical Specifications

Brand	Stahlin	Integral Mounting Flange	Yes
Item	Enclosure	Dual Access	No
Series	JW	Knockouts	No
Subpanel	Purchase subpanel separately	Bottom Gland Plate	No
Slope Top	No	Material	Fiberglass reinforced polyester
3-Piece Assembly	No	Color	Gray
Vented	No	Cover Type	Single-door
NEMA Rating	1/3R/4X/6P/12	Hinge Type	Continuous hinge
IP Rating	IP66	Number of Hinges Per Door	1
Nominal Enclosure Dimensions	6 x 6 x 4in (HxWxD)	Latch Type	(1) quick-release latch
Enclosure Height	7.50in	Padlock Attachment Type	Padlock hasp and staple
Enclosure Width	7.50in	Shelf	No
Enclosure Depth	4.75in	Window Material	SAR acrylic
Mounting	Wall	Padlockable	Yes
Integral Mounting Feet	No	Keylocking	No

Agency Approvals

UL Listed File #	E64358	E362920
UL Recognized File #	E333478	
UL Hazardous File #	None	
CE	View CE declarations	
CSA File #	LR069014	
RoHS Status	Yes (See CE Doc)	
EU REACH	View EU REACH document	

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/JW606HPL.pdf>
See store item page for other formats.