

K2BB-3/4 Cut Sheet



Greenlee Slug-Buster knockout punch and die, 3/4in conduit.
Punch, die and 3/4in draw stud included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/K2BB-3/4>

Technical Specifications

| | |
|--------------------------------|---|
| Brand | Greenlee |
| Series | Slug-Buster |
| Item | Knockout punch and die |
| Replacement | No |
| Knockout Size | 3/4in conduit |
| Punch Shape | Round |
| Nominal Hole Size | 1.12in (28.3 mm) |
| Maximum Punch Thickness | 10ga mild steel |
| Application | Hole cutting |
| For Use On | Steel, plastic, stainless steel and non-ferrous metals |
| Includes | Punch, die and 3/4in draw stud |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |