

# K2LC-D2-115-230 Cut Sheet



Klemsan remote level controller, tank fill, tank drain and transfer, (4) conductive level probes and (1) common probe input, (1) SPDT non-latching relay, adjustable time delay output, 115/230 VAC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/K2LC-D2-115-230>

## Technical Specifications

|                        |                                                     |
|------------------------|-----------------------------------------------------|
| Brand                  | Klemsan                                             |
| Item                   | Remote level controller                             |
| Application            | Tank fill, tank drain and transfer                  |
| Input                  | (4) conductive level probes and (1) common probe    |
| Output                 | (1) SPDT non-latching relay, adjustable time delay  |
| Operating Voltage      | 115/230 VAC                                         |
| Indicating Type        | LED indicators for min, max, power and relay status |
| Mounting               | 35mm DIN rail or through panel                      |
| Additional Information | Order Klemsan SE-1 probes separately                |

## Agency Approvals

|                      |                                        |
|----------------------|----------------------------------------|
| UL Listed File #     | E542919                                |
| UL Recognized File # | None                                   |
| UL Hazardous File #  | None                                   |
| CE                   | <a href="#">View CE declarations</a>   |
| CSA File #           | None                                   |
| RoHS Status          | Yes (See CE Doc)                       |
| EU REACH             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/K2LC-D2-115-230.pdf>  
See store item page for other formats.