

# K3BB-2 Cut Sheet



Greenlee Standard Round knockout punch and die, 2in conduit.  
Punch, die and 3/4in draw stud included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/K3BB-2>

---

## Technical Specifications

|                                |   |
|--------------------------------|---|
| <b>Brand</b>                   | Greenlee  |
| <b>Series</b>                  | Standard Round  |
| <b>Item</b>                    | Knockout punch and die                                    |
| <b>Replacement</b>             | No  |
| <b>Knockout Size</b>           | 2in conduit   |
| <b>Punch Shape</b>             | Round   |
| <b>Nominal Hole Size</b>       | 2.42in (61.5 mm)  |
| <b>Maximum Punch Thickness</b> | 10ga mild steel   |
| <b>Application</b>             | Hole cutting  |
| <b>For Use On</b>              | Steel, plastic, stainless steel<br>and non-ferrous metals |
| <b>Includes</b>                | Punch, die and 3/4in draw stud                            |

---

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | None                                   |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | None                                   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | No                                     |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |