

K3P-300-UVAC Cut Sheet



AutomationDirect (Eaton) molded case circuit breaker, 400A frame, 300A, 600 VAC / 250 VDC, 3-pole, characteristics, thermal magnetic, 35kA @ 480 VAC interrupting rating, panel mount. Line and load lug terminals and factory installed 120 VAC undervoltage release included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/K3P-300-UVAC>

Technical Specifications

Brand	AutomationDirect (Eaton)
Item	Circuit breaker
Circuit Breaker Type	Molded case
Circuit Type	Feeder and branch
Current-Limiting	No
Frame Size	400A frame
Amperage Rating	300A
Voltage Rating	600 VAC / 250 VDC
Number of Poles	3

Trip Curve	Characteristics
Trip Type	Thermal magnetic
Interrupting Rating	35kA @ 480 VAC
UL Rating	UL 489 listed
Mounting	Panel
HACR Rated	Yes
Reverse Feed Capable	No
Includes	Line and load lug terminals and factory installed 120 VAC undervoltage release

Agency Approvals

UL Listed File #	E503708
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	43556
RoHS Status	No
EU REACH	View EU REACH document