

KC1234-25 Cut Sheet



Minerallac conduit mount spring clip, UL Type UL 2239. Package of 25. For use with 1/2in or 3/4in conduit.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/KC1234-25>

Technical Specifications

Brand	Minerallac
Item	Spring clip
Mount Type	Conduit mount
Mounting Hole Size	1/4in
Material	Spring steel
Finish	Zinc phosphate plated
Outside Diameter	0.70-1.05in
Tubing Size	3/4in, 13/16in, 7/8in, 15/16in and 1in
Rigid Metallic Conduit (RMC) Trade Size	1/2in and 3/4in
Electrical Metallic Tubing (EMT) Trade Size	1/2in and 3/4in

Intermediate Metallic Conduit (IMC) Trade Size	1/2in and 3/4in
Reduced Wall Flexible Metal Conduit Trade Size	3/8in and 1/2in
Liquid-tight Flexible Metal Conduit (LFMC) Trade Size	1/2in and 3/4in
UL Type	UL 2239
Quantity per Pack	25
For Use With	1/2in or 3/4in conduit

Agency Approvals

UL Listed File #	E165884
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document