

KC38 Cut Sheet



Minerallac conduit mount spring clip, UL Type UL 2239. Package of 100. For use with 3/8in conduit.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/KC38>

Technical Specifications

Brand	Minerallac
Item	Spring clip
Mount Type	Conduit mount
Mounting Hole Size	1/4in
Material	Spring steel
Finish	Zinc phosphate plated
Outside Diameter	0.51in
Tubing Size	1/2in
Rigid Metallic Conduit (RMC) Trade Size	3/8in
Electrical Metallic Tubing (EMT) Trade Size	3/8in

Intermediate Metallic Conduit (IMC) Trade Size	3/8in
Reduced Wall Flexible Metal Conduit Trade Size	3/8in
Liquid-tight Flexible Metal Conduit (LFMC) Trade Size	3/8in
BX Armored Cable Size	14-2, 14-3 and 12-2
UL Type	UL 2239
Quantity per Pack	100
For Use With	3/8in conduit

Agency Approvals

UL Listed File #	E165884
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document