

# KL1-SS-220005 Cut Sheet



IDEM safety switch, tongue (key) interlock, solenoid, 110 VAC to unlock, 180-degree adjustable head, 1600N holding force, (2) N.C. safety output(s), (2) N.O. monitoring output(s), 316 stainless steel body, (1) 1/2in NPT cable entry.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/KL1-SS-220005>

## Technical Specifications

Brand	IDEM
Item	Safety switch
Actuator Type	Tongue (key) interlock
Lock Type	Solenoid, 110 VAC to unlock
Head Type	180-degree adjustable
Holding Force	1600N
Safety Output Type	(2) N.C.
Monitoring Output Type	(2) N.O.

Indicating Type	(1) solenoid status LED
Housing Size	63 x 143 x 41mm
Body Material	316 stainless steel
Head Material	316 stainless steel
IP Rating	IP69K
Connection	(1) 1/2in NPT cable entry
Includes	(1) tamper-proof T20 Torx bit

## Agency Approvals

UL Listed File #	E258676
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/KL1-SS-220005.pdf>  
See store item page for other formats.