

KL3-SS-205005 Cut Sheet



IDEM safety switch, tongue (key) interlock, solenoid, 110 VAC to unlock, 90-degree adjustable head, 2000N holding force, (4) N.C. safety output(s), (1) N.O. monitoring output(s), 316 stainless steel body, (3) 1/2in NPT cable entries.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/KL3-SS-205005>

Technical Specifications

| | |
|-------------------------------|---|
| Brand | IDEM |
| Item | Safety switch |
| Actuator Type | Tongue (key) interlock |
| Lock Type | Solenoid, 110 VAC to unlock |
| Head Type | 90-degree adjustable |
| Holding Force | 2000N |
| Safety Output Type | (4) N.C. |
| Monitoring Output Type | (1) N.O. |
| Additional Contacts | (1) selectable output (N.O. auxiliary or LED) for lock status |
| Indicating Type | (1) solenoid status LED |
| Housing Size | 48 x 177 x 46mm |
| Body Material | 316 stainless steel |
| Head Material | 316 stainless steel |
| IP Rating | IP69K |
| Connection | (3) 1/2in NPT cable entries |
| Includes | (1) tamper-proof T20 Torx bit |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E258676 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |