

KLM-202005 Cut Sheet



IDEM safety switch, tongue (key) interlock, solenoid, 110 VAC to unlock, 90-degree adjustable head, 2000N holding force, (4) N.C. safety output(s), (1) N.O. monitoring output(s), die-cast aluminum body, (3) 1/2in NPT cable entries.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/KLM-202005>

Technical Specifications

Brand	IDEM
Item	Safety switch
Actuator Type	Tongue (key) interlock
Lock Type	Solenoid, 110 VAC to unlock
Head Type	90-degree adjustable
Holding Force	2000N
Safety Output Type	(4) N.C.
Monitoring Output Type	(1) N.O.
Additional Contacts	(1) selectable output (N.O. auxiliary or LED) for lock status
Indicating Type	(1) solenoid status LED, (1) selectable lock status LED
Housing Size	46 x 176 x 46mm
Body Material	Die-cast aluminum
Head Material	Die-cast aluminum
IP Rating	IP67
Connection	(3) 1/2in NPT cable entries
Includes	(1) tamper-proof T20 Torx bit

Agency Approvals

UL Listed File #	E258676
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document