

KLP-201005 Cut Sheet



IDEM safety switch, tongue (key) interlock, solenoid, 110 VAC to unlock, 90-degree adjustable head, 1800N holding force, (2) N.C. safety output(s), (1) N.O. monitoring output(s), plastic body, (1) 1/2in NPT cable entry.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/KLP-201005>

Technical Specifications

Brand	IDEM
Item	Safety switch
Actuator Type	Tongue (key) interlock
Lock Type	Solenoid, 110 VAC to unlock
Head Type	90-degree adjustable
Holding Force	1800N
Safety Output Type	(2) N.C.
Monitoring Output Type	(1) N.O.
Additional Contacts	(1) selectable output (N.O. auxiliary or LED) for lock status

Indicating Type	(1) solenoid status LED, (1) selectable lock status LED
Housing Size	46 x 160 x 45mm
Body Material	Plastic
Head Material	316 stainless steel
IP Rating	IP67
Connection	(1) 1/2in NPT cable entry
Includes	(1) tamper-proof T20 Torx bit

Agency Approvals

UL Listed File #	E258676
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/KLP-201005.pdf>
See store item page for other formats.