

KLTM-450005 Cut Sheet



IDEM safety switch, tongue (key) interlock, solenoid, 110 VAC to unlock, 180-degree adjustable head, 2000N holding force, (4) N.C. safety output(s), (1) N.O. monitoring output(s), die-cast aluminum body, (3) 1/2in NPT cable entries.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/KLTM-450005>

Technical Specifications

Brand	IDEM
Item	Safety switch
Actuator Type	Tongue (key) interlock
Lock Type	Solenoid, 110 VAC to unlock
Head Type	180-degree adjustable
Holding Force	2000N
Safety Output Type	(4) N.C.
Monitoring Output Type	(1) N.O.
Indicating Type	(1) solenoid status LED, (1) selectable lock status LED
Housing Size	105 x 150 x 41mm
Body Material	Die-cast aluminum
Head Material	316 stainless steel
IP Rating	IP67
Connection	(3) 1/2in NPT cable entries
Includes	(1) tamper-proof T20 Torx bit

Agency Approvals

UL Listed File #	E258676
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document