

KM-203011 Cut Sheet



IDEM safety switch, tongue (key) interlock, 90-degree adjustable head, (2) N.C. safety output(s), (2) N.O. monitoring output(s), 40 x 118 x 41mm, die-cast aluminum body, die-cast aluminum head.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/KM-203011>

Technical Specifications

Brand	IDEM
Item	Safety switch
Actuator Type	Tongue (key) interlock
Head Type	90-degree adjustable
Action	Slow action break before make
Safety Output Type	(2) N.C.
Monitoring Output Type	(2) N.O.
Housing Size	40 x 118 x 41mm
Body Material	Die-cast aluminum
Head Material	Die-cast aluminum
IP Rating	IP67
Connection	(1) 1/2in NPT cable entry
Includes	(1) tamper-proof T20 Torx bit

Agency Approvals

UL Listed File #	E258676
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/KM-203011.pdf>
See store item page for other formats.