

KM-SS-204011 Cut Sheet



IDEM safety switch, tongue (key) interlock, 90-degree adjustable head, (2) N.C. safety output(s), (2) N.O. monitoring output(s), 41 x 118 x 41mm, 316 stainless steel body, 316 stainless steel head.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/KM-SS-204011>

Technical Specifications

| | |
|-------------------------------|-------------------------------|
| Brand | IDEM |
| Item | Safety switch |
| Actuator Type | Tongue (key) interlock |
| Head Type | 90-degree adjustable |
| Action | Slow action break before make |
| Safety Output Type | (2) N.C. |
| Monitoring Output Type | (2) N.O. |
| Housing Size | 41 x 118 x 41mm |
| Body Material | 316 stainless steel |
| Head Material | 316 stainless steel |
| IP Rating | IP69K |
| Connection | (1) 1/2in NPT cable entry |
| Includes | (1) tamper-proof T20 Torx bit |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E258676 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |