

KN-D10BLK Cut Sheet



Konnect-It screw double-level feedthrough terminal block, accepts wire size 26-10 AWG, black, 30A, 35mm DIN rail mount, 100kA SCCR. Package of 100. For use with jumpers KN-2J10, KN-3J10, KN-4J10 and KN-10J10.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/KN-D10BLK>

Technical Specifications

| | |
|---------------------|--|
| Brand | Konnect-It |
| Item | Terminal block |
| Connector Type | Screw |
| Terminal Block Type | Double-level feedthrough |
| Wire Size | 26-10 AWG |
| Color | Black |
| Amperage Rating | 30A |
| Voltage Rating | 300V rated (UL) |
| Mounting | 35mm DIN rail |
| SCCR Rating | 100kA SCCR |
| Quantity per Pack | 100 |
| For Use With | Jumpers KN-2J10, KN-3J10, KN-4J10 and KN-10J10 |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | None |
| UL Recognized File # | E179129 |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/KN-D10BLK.pdf>
See store item page for other formats.