

KN-FRK10DBL Cut Sheet



Konnect-It fork feedthrough terminal block, single-level, 2 inputs to 2 outputs, M4 screw, accepts wire size 20–10 AWG, gray, 41A, 300 VAC/VDC, 35mm DIN rail mount. Package of 25.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/KN-FRK10DBL>

Technical Specifications

Brand	Konnect-It
Item	Terminal block
Connector Type	Fork
Terminal Block Type	Feedthrough
Number of Levels	1
Number of Inputs	2
Number of Outputs	2
Interior Connection Type	2 inputs to 2 outputs, M4 screw

Wire Size	20–10 AWG
Color	Gray
Amperage Rating	41A
Voltage Rating	300 VAC/VDC
Mounting	35mm DIN rail
SCCR Rating	10 kA SCCR
Quantity per Pack	25

Agency Approvals

UL Listed File #	None
UL Recognized File #	E179129
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	None

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/KN-FRK10DBL.pdf>
See store item page for other formats.