

KN-FS4-20 Cut Sheet



Konnect-It quick connect feedthrough terminal block, single-level, 12–2.8mm or 6–6.3mm connections, accepts wire size 28–12 AWG, gray, 23A, 600 VAC/VDC, 35mm DIN rail mount. Package of 20.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/KN-FS4-20>

Technical Specifications

Brand	Konnect-It
Item	Terminal block
Connector Type	Quick connect
Terminal Block Type	Feedthrough
Number of Levels	1
Interior Connection Type	12–2.8mm or 6–6.3mm connections
Wire Size	28–12 AWG

Color	Gray
Amperage Rating	23A
Voltage Rating	600 VAC/VDC
Mounting	35mm DIN rail
SCCR Rating	10 kA SCCR
Quantity per Pack	20

Agency Approvals

UL Listed File #	None
UL Recognized File #	E179129
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	None

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/KN-FS4-20.pdf>
See store item page for other formats.