

KN-FSK5GRY Cut Sheet



Konnect-It screw circuit protection terminal block, single-level, fuse holder, no indicator, accepts wire size 26–10 AWG, gray, 10A, 300 VAC/VDC, 35mm DIN rail mount. Package of 50.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/KN-FSK5GRY>

Technical Specifications

Brand	Konnect-It
Item	Terminal block
Connector Type	Screw
Terminal Block Type	Circuit protection
Number of Levels	1
Number of Inputs	1
Number of Outputs	1
Interior Connection Type	Fuse holder, no indicator
Accepts Fuse Class	Small dimension (5x20mm and 5x25mm)
Fuse Type	GMA, GMC, S500 and S506 series fuses

Wire Size	26–10 AWG
Color	Gray
Amperage Rating	10A
Voltage Rating	300 VAC/VDC
Mounting	35mm DIN rail
SCCR Rating	10 kA SCCR
Quantity per Pack	50
For Use With	Jumpers KN-10JFSK5, KN-2JFSK5, KN-3JFSK5 and KN-4JFSK5

Agency Approvals

UL Listed File #	None
UL Recognized File #	E179129
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	None

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/KN-FSK5GRY.pdf>
See store item page for other formats.