

# KN-GRNG2P5 Cut Sheet



Konnect-It ring grounding terminal block, single-level, M3 stud, accepts wire size 26–14 AWG, yellow/green, 35mm DIN rail mount. Package of 20.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/KN-GRNG2P5>

## Technical Specifications

<b>Brand</b>	Konnect-It
<b>Item</b>	Terminal block
<b>Connector Type</b>	Ring
<b>Terminal Block Type</b>	Grounding
<b>Number of Levels</b>	1
<b>Number of Inputs</b>	1
<b>Number of Outputs</b>	1

<b>Interior Connection Type</b>	M3 stud
<b>Wire Size</b>	26–14 AWG
<b>Color</b>	Yellow/green
<b>Mounting</b>	35mm DIN rail
<b>SCCR Rating</b>	10 kA SCCR
<b>Quantity per Pack</b>	20

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E179129
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	608873
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	None

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/KN-GRNG2P5.pdf>  
See store item page for other formats.