

KN-GRNG6-20 Cut Sheet



Konnect-It ring grounding terminal block, single-level, M4 stud, accepts wire size 22–8 AWG, yellow/green, 35mm DIN rail mount. Package of 20.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/KN-GRNG6-20>

Technical Specifications

Brand	Konnect-It
Item	Terminal block
Connector Type	Ring
Terminal Block Type	Grounding
Number of Levels	1
Number of Inputs	1
Number of Outputs	1

Interior Connection Type	M4 stud
Wire Size	22–8 AWG
Color	Yellow/green
Mounting	35mm DIN rail
SCCR Rating	10 kA SCCR
Quantity per Pack	20

Agency Approvals

UL Listed File #	None
UL Recognized File #	E179129
UL Hazardous File #	None
CE	View CE declarations
CSA File #	608873
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	None

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/KN-GRNG6-20.pdf>
See store item page for other formats.