

KN-GRNG6 Cut Sheet



Konnect-It ring grounding terminal block, single-level, M4 stud, accepts wire size 22–8 AWG, yellow/green, 35mm DIN rail mount. Package of 40.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/KN-GRNG6>

Technical Specifications

| | |
|----------------------------|----------------|
| Brand | Konnect-It |
| Item | Terminal block |
| Connector Type | Ring |
| Terminal Block Type | Grounding |
| Number of Levels | 1 |
| Number of Inputs | 1 |
| Number of Outputs | 1 |

| | |
|---------------------------------|---------------|
| Interior Connection Type | M4 stud |
| Wire Size | 22–8 AWG |
| Color | Yellow/green |
| Mounting | 35mm DIN rail |
| SCCR Rating | 10 kA SCCR |
| Quantity per Pack | 40 |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | E179129 |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | 608873 |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |
| Other | None |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/KN-GRNG6.pdf>
See store item page for other formats.