


KN-MG10-10 Cut Sheet



Konnect-It screw mini grounding terminal block, accepts wire size 26-10 AWG, green and yellow, 15mm DIN rail mount, 100kA SCCR. Package of 10. Use to mechanically and electrically connect wires to 15mm DIN rail through the snap-on clamping foot.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/KN-MG10-10>

Technical Specifications

Brand	Konnect-It
Item	Terminal block
Connector Type	Screw
Terminal Block Type	Mini grounding
Wire Size	26-10 AWG
Color	Green and yellow
Mounting	15mm DIN rail
SCCR Rating	100kA SCCR
Quantity per Pack	10
Application	Use to mechanically and electrically connect wires to 15mm DIN rail through the snap-on clamping foot

Agency Approvals

UL Listed File #	None
UL Recognized File #	E179129
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document