

KN-T4GRY-25 Cut Sheet



Konnect-It screw single-level feedthrough terminal block, accepts wire size 12-4 AWG, gray, 80A, 35mm DIN rail mount, 100kA SCCR. Package of 25. For use with jumpers KN-2J4, KN-3J4, KN-4J4 or KN-10J4.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/KN-T4GRY-25>

Technical Specifications

Brand	Konnect-It
Item	Terminal block
Connector Type	Screw
Terminal Block Type	Single-level feedthrough
Wire Size	12-4 AWG
Color	Gray
Amperage Rating	80A
Voltage Rating	600V rated (UL)
Mounting	35mm DIN rail
SCCR Rating	100kA SCCR
Quantity per Pack	25
For Use With	Jumpers KN-2J4, KN-3J4, KN-4J4 or KN-10J4

Agency Approvals

UL Listed File #	None
UL Recognized File #	E179129
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document