


# KN-T6WHT-50 Cut Sheet



Konnect-It screw single-level feedthrough terminal block, accepts wire size 16-6 AWG, white, 65A, 35mm DIN rail mount, 100kA SCCR. Package of 50. For use with jumpers KN-2J6, KN-3J6, KN-4J6 and KN-10J6.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/KN-T6WHT-50>

## Technical Specifications

<b>Brand</b>	Konnect-It
<b>Item</b>	Terminal block
<b>Connector Type</b>	Screw
<b>Terminal Block Type</b>	Single-level feedthrough
<b>Wire Size</b>	16-6 AWG
<b>Color</b>	White
<b>Amperage Rating</b>	65A
<b>Voltage Rating</b>	300 VAC/VDC (UL usage groups B & C), 600 VAC/VDC (UL usage group D)
<b>Mounting</b>	35mm DIN rail
<b>SCCR Rating</b>	100kA SCCR
<b>Quantity per Pack</b>	50
<b>For Use With</b>	Jumpers KN-2J6, KN-3J6, KN-4J6 and KN-10J6

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E179129
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>