


# KN-TL14SLN Cut Sheet



Konnect-It screw triple-level sensor terminal block, connected between levels and power indicator, accepts wire size 24-12 AWG, gray, 24A, NPN LED indicator(s), 35mm DIN rail mount, 100kA SCCR. Package of 20.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/KN-TL14SLN>

## Technical Specifications

<b>Brand</b>	Konnect-It
<b>Item</b>	Terminal block
<b>Connector Type</b>	Screw
<b>Terminal Block Type</b>	Triple-level sensor
<b>Terminal Block Special Feature(s)</b>	Connected between levels and power indicator
<b>Wire Size</b>	24-12 AWG
<b>Color</b>	Gray
<b>Amperage Rating</b>	24A
<b>Voltage Rating</b>	24 VDC
<b>Indicator</b>	NPN LED
<b>Mounting</b>	35mm DIN rail
<b>SCCR Rating</b>	100kA SCCR
<b>Quantity per Pack</b>	20
<b>For Use With</b>	Jumpers KN-2JTL12, KN-3JTL12, KN-4JTL12 and KN-10JTL12
<b>Application</b>	For NPN type sensors

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E179129
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>