

# KN-VFS4 Cut Sheet



Konnect-It quick connect/screw feedthrough terminal block, single-level, 8–2.8mm or 4–6.3mm connections, 1 screw terminal, accepts wire size 28–12 AWG, gray, 23A, 600 VAC/VDC, 35mm DIN rail mount. Package of 80.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/KN-VFS4>

## Technical Specifications

<b>Brand</b>	Konnect-It
<b>Item</b>	Terminal block
<b>Connector Type</b>	Quick connect/screw
<b>Terminal Block Type</b>	Feedthrough
<b>Number of Levels</b>	1
<b>Interior Connection Type</b>	8–2.8mm or 4–6.3mm connections, 1 screw terminal
<b>Wire Size</b>	28–12 AWG

<b>Color</b>	Gray
<b>Amperage Rating</b>	23A
<b>Voltage Rating</b>	600 VAC/VDC
<b>Mounting</b>	35mm DIN rail
<b>SCCR Rating</b>	10 kA SCCR
<b>Quantity per Pack</b>	80

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E179129
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	None

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/KN-VFS4.pdf>  
See store item page for other formats.