

KP06MD-M Cut Sheet



NITRA pneumatic gripper, parallel, double acting, 6mm bore, 4mm stroke, side mount grip, anodized aluminum body, M3 x 0.5 threaded port(s).

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/KP06MD-M>

Technical Specifications

| | |
|---------------------------------|-------------------|
| Brand | NITRA |
| Item | Gripper |
| Working Fluid | Pneumatic |
| Grip Type | Parallel |
| Action Type | Double acting |
| Bore Diameter | 6mm |
| Stroke | 4mm |
| Grip Mount Style | Side |
| Body Material | Anodized aluminum |
| Port Information | M3 x 0.5 threaded |
| Repeatability | +/- 0.01mm |
| Cycle Rate | 180 cyc/min |
| Resulting Gripper Travel | 4mm |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |