


KP10MSA-MB Cut Sheet



NITRA pneumatic gripper, parallel, single acting, N.O., 10mm bore, 4mm stroke, end mount grip, anodized aluminum body, M3 x 0.5 threaded port(s).

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/KP10MSA-MB>

Technical Specifications

Brand	NITRA
Item	Gripper
Working Fluid	Pneumatic
Grip Type	Parallel
Action Type	Single acting
Operation Mode	N.O.
Bore Diameter	10mm
Stroke	4mm
Grip Mount Style	End
Body Material	Anodized aluminum
Port Information	M3 x 0.5 threaded
Repeatability	+/- 0.01mm
Cycle Rate	180 cyc/min
Resulting Gripper Travel	4mm

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document