


KPR-SCF-115VACDC-1 Cut Sheet



Klemsan interface relay, 35mm DIN rail mount, finger-safe, 115 VAC/VDC coil voltage, SPDT, (1) N.O., (1) N.C., 6A contact rating, screw terminal(s), LED indicator(s). Integrated leakage current suppression filter.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/KPR-SCF-115VACDC-1>

Technical Specifications

| | |
|------------------------|---|
| Brand | Klemsan |
| Item | Relay |
| Relay Type | Interface |
| Mounting | 35mm DIN rail |
| Relay Housing Type | Finger-safe |
| Coil Voltage | 115 VAC/VDC |
| Relay Configuration | SPDT |
| Output Type | (1) N.O., (1) N.C. |
| Contact Rating | 6A |
| Connector Type | Screw terminal(s) |
| Indicator | LED |
| Additional Information | Integrated leakage current suppression filter |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | E361956 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |