

KT-V4S-C-D Cut Sheet



JTEKT multi-mode digital timer, two-line red/green LED display, fully selectable timing range, 10-30 VDC operating voltage, (1) NPN transistor and (1) SPDT relay output(s), 1/16 DIN mount, screw terminal(s). Panel mounting clip included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/KT-V4S-C-D>

Technical Specifications

Brand	JTEKT
Item	Digital timer
Timer Type	Multi-mode
Display Type	Two-line red/green LED display
Timing Range	Fully selectable
Operating Voltage	10-30 VDC
Timer Output Type(s)	(1) NPN transistor and (1) SPDT relay
Timer Function(s)	<ul style="list-style-type: none">• on-delay• off-delay• single-shot• accumulation• flicker
Mounting	1/16 DIN
Connector Type	Screw terminal(s)
Includes	Panel mounting clip

Agency Approvals

UL Listed File #	None
UL Recognized File #	E186879
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document