

L10 Cut Sheet



Fibox hinged enclosure window, 7.87 x 3.03in window, polycarbonate, 7.87 x 3.03in frame, polycarbonate, RAL 7035 light gray, EPDM gasket. For use with IP65 enclosures. Mounting hardware included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/L10>

Technical Specifications

Brand	Fibox
Item	Hinged enclosure window
Window Size	7.87 x 3.03in
Window Material	Polycarbonate
Frame Size	7.87 x 3.03in
Frame Material	Polycarbonate
Color	RAL 7035 light gray
Gasket Type	EPDM
Cutout Size	7.20 x 1.97in
For Use With	IP65 enclosures
Includes	Mounting hardware

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/L10.pdf>
See store item page for other formats.