

L221004-1 Cut Sheet



Lapp OLFLEX Tray II flexible power/control cable, unshielded, 4 conductors (includes ground), 10 AWG, bare copper, PVC/Nylon conductor insulation material, black with white numbers and green/yellow ground, PVC jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/L221004-1>

Technical Specifications

Brand	Lapp
Item	Cable
Series	OLFLEX Tray II
Wire/Cable Type	Power/control
UL Wire/Cable Type	ITC-ER, TC-ER, WTTTC, DP-1 and MTW
Applicable Standards	UL 1277, UL 2277, UL 1690, UL 83, ECOLAB, direct burial and submersible pump
Application	General purpose
Flexibility	Flexible
Voltage Rating	600V (Types TC-ER), 1000V (Type WTTTC)
Conductors	4 conductors (includes ground)
Conductor Size	10 AWG

Conductor Stranding	84-stranded
Conductor Material	Bare copper
Conductor Insulation Material	PVC/Nylon
Conductor Insulation Color	Black with white numbers and green/yellow ground
Shielding	Unshielded
Jacket Material	PVC
Jacket Color	Black
Nominal Overall Cable Diameter	0.579in
Bulk Length	Cut to length

Agency Approvals

UL Listed File #	E171371
UL Recognized File #	E100338
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LL94629
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document