

L221607-1 Cut Sheet



Lapp OLFLEX Tray II flexible power/control cable, unshielded, 7 conductors (includes ground), 16 AWG, bare copper, PVC/Nylon conductor insulation material, black with white numbers and green/yellow ground, PVC jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/L221607-1>

Technical Specifications

Brand	Lapp
Item	Cable
Series	OLFLEX Tray II
Wire/Cable Type	Power/control
UL Wire/Cable Type	ITC-ER, TC-ER, WTTC, DP-1, MTW and PLTC-ER
Applicable Standards	UL 1277, UL 2277, UL 1690, ECOLAB and direct burial
Application	General purpose
Flexibility	Flexible
Voltage Rating	600V (Types ITC-ER, TC-ER, PLTC-ER), 1000V (Type WTTC)
Conductors	7 conductors (includes ground)

Conductor Size	16 AWG
Conductor Stranding	30-stranded
Conductor Material	Bare copper
Conductor Insulation Material	PVC/Nylon
Conductor Insulation Color	Black with white numbers and green/yellow ground
Shielding	Unshielded
Jacket Material	PVC
Jacket Color	Black
Nominal Overall Cable Diameter	0.413in
Bulk Length	Cut to length

Agency Approvals

UL Listed File #	E171371
UL Recognized File #	E100338
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LL94629
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document