

# L221802-1 Cut Sheet



Lapp OLFLEX Tray II flexible power/control cable, unshielded, 2 conductors, 18 AWG, bare copper, PVC/Nylon conductor insulation material, black with white numbers, PVC jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/L221802-1>

## Technical Specifications

|                             |                                                     |                                       |                          |
|-----------------------------|-----------------------------------------------------|---------------------------------------|--------------------------|
| <b>Brand</b>                | Lapp                                                | <b>Conductor Size</b>                 | 18 AWG                   |
| <b>Item</b>                 | Cable                                               | <b>Conductor Stranding</b>            | 32-stranded              |
| <b>Series</b>               | OLFLEX Tray II                                      | <b>Conductor Material</b>             | Bare copper              |
| <b>Wire/Cable Type</b>      | Power/control                                       | <b>Conductor Insulation Material</b>  | PVC/Nylon                |
| <b>UL Wire/Cable Type</b>   | ITC, TC, PLTC, WTTTC, DP-1 and MTW                  | <b>Conductor Insulation Color</b>     | Black with white numbers |
| <b>Applicable Standards</b> | UL 1277, UL 2277, UL 1690, ECOLAB and direct burial | <b>Shielding</b>                      | Unshielded               |
| <b>Application</b>          | General purpose                                     | <b>Jacket Material</b>                | PVC                      |
| <b>Flexibility</b>          | Flexible                                            | <b>Jacket Color</b>                   | Black                    |
| <b>Voltage Rating</b>       | 600V (Types ITC, TC, PLTC), 1000V (Type WTTTC)      | <b>Nominal Overall Cable Diameter</b> | 0.283in                  |
| <b>Conductors</b>           | 2 conductors                                        | <b>Bulk Length</b>                    | Cut to length            |

## Agency Approvals

|                             |                                        |
|-----------------------------|----------------------------------------|
| <b>UL Listed File #</b>     | E171371                                |
| <b>UL Recognized File #</b> | E100338                                |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | LL94629                                |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |