

L221818-1 Cut Sheet



Lapp OLFLEX Tray II flexible power/control cable, unshielded, 18 conductors (includes ground), 18 AWG, bare copper, PVC/ Nylon conductor insulation material, black with white numbers and green/yellow ground, PVC jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/L221818-1>

Technical Specifications

Brand	Lapp	Conductor Size	18 AWG
Item	Cable	Conductor Stranding	32-stranded
Series	OLFLEX Tray II	Conductor Material	Bare copper
Wire/Cable Type	Power/control	Conductor Insulation Material	PVC/Nylon
UL Wire/Cable Type	ITC-ER, TC-ER, WTTC, DP-1, MTW and PLTC-ER	Conductor Insulation Color	Black with white numbers and green/yellow ground
Applicable Standards	UL 1277, UL 2277, UL 1690, ECOLAB and direct burial	Shielding	Unshielded
Application	General purpose	Jacket Material	PVC
Flexibility	Flexible	Jacket Color	Black
Voltage Rating	600V (Types ITC-ER, TC-ER, PLTC-ER), 1000V (Type WTTC)	Nominal Overall Cable Diameter	0.587in
Conductors	18 conductors (includes ground)	Bulk Length	Cut to length

Agency Approvals

UL Listed File #	E171371
UL Recognized File #	E100338
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LL94629
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document