

# L25M0800MD-MC Cut Sheet

NITRA pneumatic cylinder, rodless, 25mm bore, 800mm stroke, double acting, magnetic piston, front and rear adjustable cushions, tapped end caps mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/L25M0800MD-MC>

## Technical Specifications

<b>Brand</b>	NITRA
<b>Item</b>	Cylinder
<b>Working Fluid</b>	Air
<b>Cylinder Type</b>	Rodless
<b>Bore Diameter</b>	25mm
<b>Stroke</b>	800mm
<b>Port Size</b>	G1/8 female BSPP
<b>Mounting</b>	Tapped end caps
<b>Action Type</b>	Double acting
<b>Magnetic Piston</b>	Magnetic piston
<b>Adjustable Cushions</b>	Front and rear adjustable cushions
<b>Body Material</b>	Aluminum
<b>End Cap Material</b>	Aluminum

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/L25M0800MD-MC.pdf>  
See store item page for other formats.