

L32M0800MD-MC Cut Sheet

NITRA pneumatic cylinder, rodless, 32mm bore, 800mm stroke, double acting, magnetic piston, front and rear adjustable cushions, tapped end caps mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/L32M0800MD-MC>

Technical Specifications

Brand	NITRA
Item	Cylinder
Working Fluid	Air
Cylinder Type	Rodless
Bore Diameter	32mm
Stroke	800mm
Port Size	G1/4 female BSPP
Mounting	Tapped end caps
Action Type	Double acting
Magnetic Piston	Magnetic piston
Adjustable Cushions	Front and rear adjustable cushions
Body Material	Aluminum
End Cap Material	Aluminum

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/L32M0800MD-MC.pdf>
See store item page for other formats.