

# L601802-1 Cut Sheet



Lapp OLFLEX 190 flexible control cable, unshielded, 2 conductors, 18 AWG, bare copper, PVC conductor insulation material, black with white numbers, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/L601802-1>

## Technical Specifications

<b>Brand</b>	Lapp
<b>Item</b>	Cable
<b>Series</b>	OLFLEX 190
<b>Wire/Cable Type</b>	Control
<b>UL Wire/Cable Type</b>	TC and WTTC
<b>Applicable Standards</b>	UL 1277, UL 2277, ECOLAB and NFPA 79
<b>Application</b>	General purpose
<b>Flexibility</b>	Flexible
<b>Voltage Rating</b>	600V (Type TC), 1000V (Type WTTC, UL/CSA AWM)
<b>Conductors</b>	2 conductors

<b>Conductor Size</b>	18 AWG
<b>Conductor Stranding</b>	32-stranded
<b>Conductor Material</b>	Bare copper
<b>Conductor Insulation Material</b>	PVC
<b>Conductor Insulation Color</b>	Black with white numbers
<b>Shielding</b>	Unshielded
<b>Jacket Material</b>	PVC
<b>Jacket Color</b>	Gray
<b>Nominal Overall Cable Diameter</b>	0.277in
<b>Bulk Length</b>	Cut to length

## Agency Approvals

<b>UL Listed File #</b>	E171371
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	LL94629
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>