

L601812-1 Cut Sheet



Lapp OLFLEX 190 flexible control cable, unshielded, 12 conductors (includes ground), 18 AWG, bare copper, PVC conductor insulation material, black with white numbers and green/yellow ground, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/L601812-1>

Technical Specifications

Brand	Lapp
Item	Cable
Series	OLFLEX 190
Wire/Cable Type	Control
UL Wire/Cable Type	TC-ER and WTTC
Applicable Standards	UL 1277, UL 2277, ECOLAB and NFPA 79
Application	General purpose
Flexibility	Flexible
Voltage Rating	600V (Type TC-ER), 1000V (Type WTTC, UL/CSA AWM)
Conductors	12 conductors (includes ground)
Conductor Size	18 AWG

Conductor Stranding	32-stranded
Conductor Material	Bare copper
Conductor Insulation Material	PVC
Conductor Insulation Color	Black with white numbers and green/yellow ground
Shielding	Unshielded
Jacket Material	PVC
Jacket Color	Gray
Nominal Overall Cable Diameter	0.471in
Bulk Length	Cut to length

Agency Approvals

UL Listed File #	E171371
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LL94629
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document