


L602002-1 Cut Sheet



Lapp OLFLEX 190 flexible control cable, unshielded, 2 conductors, 20 AWG, bare copper, PVC conductor insulation material, black with white numbers, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/L602002-1>

Technical Specifications

Brand	Lapp
Item	Cable
Series	OLFLEX 190
Wire/Cable Type	Control
UL Wire/Cable Type	PLTC
Applicable Standards	UL 13, ECOLAB and NFPA 79
Application	General purpose
Flexibility	Flexible
Voltage Rating	300V (Type PLTC), 1000V (UL/CSA AWM)
Conductors	2 conductors
Conductor Size	20 AWG

Conductor Stranding	16-stranded
Conductor Material	Bare copper
Conductor Insulation Material	PVC
Conductor Insulation Color	Black with white numbers
Shielding	Unshielded
Jacket Material	PVC
Jacket Color	Gray
Nominal Overall Cable Diameter	0.253in
Bulk Length	Cut to length

Agency Approvals

UL Listed File #	E216027
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LL94629
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document