

L602018-1 Cut Sheet



Lapp OLFLEX 190 flexible control cable, unshielded, 18 conductors (includes ground), 20 AWG, bare copper, PVC conductor insulation material, black with white numbers and green/yellow ground, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/L602018-1>

Technical Specifications

Brand	Lapp
Item	Cable
Series	OLFLEX 190
Wire/Cable Type	Control
UL Wire/Cable Type	PLTC-ER
Applicable Standards	UL 13, ECOLAB and NFPA 79
Application	General purpose
Flexibility	Flexible
Voltage Rating	300V (Type PLTC-ER), 1000V (UL/CSA AWM)
Conductors	18 conductors (includes ground)
Conductor Size	20 AWG

Conductor Stranding	16-stranded
Conductor Material	Bare copper
Conductor Insulation Material	PVC
Conductor Insulation Color	Black with white numbers and green/yellow ground
Shielding	Unshielded
Jacket Material	PVC
Jacket Color	Gray
Nominal Overall Cable Diameter	0.487in
Bulk Length	Cut to length

Agency Approvals

UL Listed File #	E216027
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LL94629
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document