

LA-12-25 Cut Sheet



Electri-Flex Liquatite liquid-tight flexible metallic conduit, hot dipped galvanized steel, PVC jacket, 3/4in trade size, gray, UL-360 Listed, 25ft/7.6m coil length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LA-12-25>

Technical Specifications

Brand	Electri-Flex	Coil Length	25ft/7.6m
Series	Liquatite	UL Rating	UL-360 Listed
Item	Conduit	Operating Temperature	-22 deg F to 176 deg F (-30 deg C to 80 deg C)
Conduit Type	Liquid-tight flexible metallic conduit (LFMC)	UV Resistant	Yes
Liquid-tight	Yes	Applicable Standards	<ul style="list-style-type: none">• ANSI/UL-360• CSA C22.2 No 56-17 Annex A Heavy duty• IEC 61386• CEC CSA 22.1-18
Inner Core Material	Hot dipped galvanized steel		
Outer Material	PVC jacket		
Trade Size	3/4in	Application	Wet and oily conditions
Color	Gray		

Agency Approvals

UL Listed File #	E29278
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LL18858
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document