

# LA-13-100 Cut Sheet



Electri-Flex Liquatite liquid-tight flexible metallic conduit, hot dipped galvanized steel, PVC jacket, 1in trade size, gray, UL-360 Listed, 100ft/30.4m coil length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LA-13-100>

## Technical Specifications

<b>Brand</b>	Electri-Flex	<b>Coil Length</b>	100ft/30.4m
<b>Series</b>	Liquatite	<b>UL Rating</b>	UL-360 Listed
<b>Item</b>	Conduit	<b>Operating Temperature</b>	-22 deg F to 176 deg F (-30 deg C to 80 deg C)
<b>Conduit Type</b>	Liquid-tight flexible metallic conduit (LFMC)	<b>UV Resistant</b>	Yes
<b>Liquid-tight</b>	Yes	<b>Applicable Standards</b>	<ul style="list-style-type: none"><li>• ANSI/UL-360</li><li>• CSA C22.2 No 56-17 Annex A Heavy duty</li><li>• IEC 61386</li><li>• CEC CSA 22.1-18</li></ul>
<b>Inner Core Material</b>	Hot dipped galvanized steel		
<b>Outer Material</b>	PVC jacket		
<b>Trade Size</b>	1in	<b>Application</b>	Wet and oily conditions
<b>Color</b>	Gray		

## Agency Approvals

<b>UL Listed File #</b>	E29278
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	LL18858
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>