

LA-13-25 Cut Sheet



Electri-Flex Liquatite liquid-tight flexible metallic conduit, hot dipped galvanized steel, PVC jacket, 1in trade size, gray, UL-360 Listed, 25ft/7.6m coil length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LA-13-25>

Technical Specifications

Brand	Electri-Flex
Series	Liquatite
Item	Conduit
Conduit Type	Liquid-tight flexible metallic conduit (LFMC)
Liquid-tight	Yes
Inner Core Material	Hot dipped galvanized steel
Outer Material	PVC jacket
Trade Size	1in
Color	Gray

Coil Length	25ft/7.6m
UL Rating	UL-360 Listed
Operating Temperature	-22 deg F to 176 deg F (-30 deg C to 80 deg C)
UV Resistant	Yes
Applicable Standards	<ul style="list-style-type: none">• ANSI/UL-360• CSA C22.2 No 56-17 Annex A Heavy duty• IEC 61386• CEC CSA 22.1-18
Application	Wet and oily conditions

Agency Approvals

UL Listed File #	E29278
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LL18858
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document