

LA-2-10 Cut Sheet



Penn-Union mechanical lug, box type, tin-plated aluminum, 600V, 1 openings, (1) 14–2 AWG stranded copper, (2) 14–10 AWG stranded copper, (1) 12–2 AWG stranded aluminum or (2) 10–12 AWG stranded aluminum, AL9CU. Package of 10.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LA-2-10>

Technical Specifications

Brand	Penn-Union
Item	Mechanical lug
Lug Type	Box type
Material	Tin-plated aluminum
Voltage Rating	600V
Number Of Openings	1
Tightening Torque	45 in-lb copper or aluminum
Conductor Bolt Style	Slotted set screw

Conductor Material	Copper or aluminum
Conductor Size	(1) 14–2 AWG stranded copper, (2) 14–10 AWG stranded copper, (1) 12–2 AWG stranded aluminum or (2) 10–12 AWG stranded aluminum
Mounting Holes	1-hole
Mounting Bolt Size	1/4in
Dual Rating	AL9CU
Quantity per Pack	10

Agency Approvals

UL Listed File #	E12822
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/LA-2-10.pdf>
See store item page for other formats.