

LC52-1001 Cut Sheet



Flowline DataPoint remote level controller, tank fill or drain and alarm, 4-20 mA level sensor input, (1) SPDT non-latching relay, (1) SPDT latching relay, adjustable time delay, 4-20 mA repeater output, 120/240 VAC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LC52-1001>

Technical Specifications

Brand	Flowline
Series	DataPoint
Item	Remote level controller
Application	Single 4-20mA level sensor automatic tank fill or drain, high or low level alarm
Input	4-20 mA level sensor
Output	(1) SPDT non-latching relay, (1) SPDT latching relay, adjustable time delay, 4-20 mA repeater
Operating Voltage	120/240 VAC
Display Type	3.5 digit LED display for level sensor
Indicating Type	LED indicators for power and relay status
Mounting	35mm DIN rail or through panel
Additional Information	Order 4-20mA level sensor separately

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document