

LE28-4P Cut Sheet



Leuze photoelectric sensor, rectangular, ABS plastic housing, through-beam receiver, 0-10m sensing distance, 10-30 VDC operating voltage, complementary light-on/dark-on, PNP, 4-wire, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LE28-4P>

Technical Specifications

| | |
|--------------------------|-----------------------|
| Brand | Leuze |
| Item | Photoelectric sensor |
| Shape | Rectangular |
| Housing Size | 57.7 x 15 x 37.3mm |
| Thread lens size | 18mm |
| IP Rating | IP67 |
| Application | Standard duty |
| Housing Material | ABS plastic |
| Sensing Method | Through-beam receiver |
| Operating Voltage | 10-30 VDC |
| Number of Wires | 4 |

| | |
|----------------------------|--------------------------------|
| Switching Output | PNP |
| Sensing Distance | 0-10m |
| Operation Mode | Complementary light-on/dark-on |
| Switching Frequency | 500 Hz |
| IO-Link Compatible | No |
| Cable Length | 6.5ft/2m |
| Jacket Material | PUR |
| Connection | Pigtail |
| Conductor Size | 24 AWG |
| Includes | Mounting hardware |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E203683 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/LE28-4P.pdf>
See store item page for other formats.