

# LHR-M18PA-PMK-603 Cut Sheet



Contrinex photoelectric sensor, tubular, threaded, ABS plastic, diffuse with background suppression, 10-250mm sensing distance, complementary light-on/dark-on, PNP, potentiometer, 700 Hz switching frequency, 6.5ft/2m cable length, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LHR-M18PA-PMK-603>

## Technical Specifications

<b>Brand</b>	Contrinex	<b>Switching Frequency</b>	700 Hz
<b>Item</b>	Photoelectric sensor	<b>Light emission</b>	Visible red
<b>Shape</b>	Tubular	<b>IO-Link Compatible</b>	Yes
<b>Barrel Type</b>	Threaded	<b>Cable Length</b>	6.5ft/2m
<b>Housing Size</b>	18mm diameter x 33mm body	<b>Jacket Material</b>	PVC
<b>IP Rating</b>	IP67	<b>Connection</b>	Pigtail
<b>Housing Material</b>	ABS plastic	<b>Communication Port and Connection Type(s)</b>	(1) 4-wire pigtail (IO-Link) port(s)
<b>Sensing Method</b>	Diffuse with background suppression	<b>Port Protocol(s)</b>	IO-Link Class A Device
<b>Operating Voltage</b>	10-30 VDC	<b>Port Speed(s)</b>	IO-Link COM2
<b>Number of Wires</b>	4	<b>IO-Link Version</b>	IO-Link v1.0
<b>Switching Output</b>	PNP	<b>Standard I/O Mode Supported</b>	Yes
<b>Sensing Distance</b>	10-250mm	<b>Includes</b>	Mounting hardware
<b>Sensitivity</b>	Potentiometer		
<b>Operation Mode</b>	Complementary light-on/dark-on		

## Agency Approvals

<b>UL Listed File #</b>	E239373
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>