

LHR-M18PA-TMS-101 Cut Sheet



Contrinex photoelectric sensor, tubular, threaded, ABS plastic, diffuse with background suppression, 10-250mm sensing distance, complementary light-on/dark-on, NPN, teach-in button, 700 Hz switching frequency, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LHR-M18PA-TMS-101>

Technical Specifications

Brand	Contrinex
Item	Photoelectric sensor
Shape	Tubular
Barrel Type	Threaded
Housing Size	18mm diameter x 27mm body
IP Rating	IP67
Housing Material	ABS plastic
Sensing Method	Diffuse with background suppression
Operating Voltage	10-30 VDC
Number of Wires	4

Switching Output	NPN
Sensing Distance	10-250mm
Sensitivity	Teach-in button
Operation Mode	Complementary light-on/dark-on
Switching Frequency	700 Hz
Light Emission	Visible red
IO-Link Compatible	No
Connection	4-pin M12 quick-disconnect
Includes	Mounting hardware
Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	E239373
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/LHR-M18PA-TMS-101.pdf>
See store item page for other formats.