

LI40-1001 Cut Sheet



Flowline PodView general purpose digital indicator, polycarbonate, NEMA 4, IP65, 6ft (1.8m) 22AWG 4-conductor cable, panel mount. For use with Flowline EchoPod DL, DS and DX series ultrasonic level sensor with firmware V50.0 or later.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LI40-1001>

Technical Specifications

Brand	Flowline
Series	PodView
Item	General purpose digital indicator
Material	Polycarbonate
NEMA Rating	4
IP Rating	IP65
Electrical Connection	6ft (1.8m) 22AWG 4-conductor cable
Mounting	Panel
For Use With	Flowline EchoPod DL, DS and DX series ultrasonic level sensor with firmware V50.0 or later
Includes	6-digit LCD display with four relay status indicators, 3-button user interface
Additional Information	Displays tank level or volume and sensor relay status

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/LI40-1001.pdf>
See store item page for other formats.